

# Product data sheet

Specifications



## SmartX Temperature Sensor, Resistive 10K Type 3 Thermistor, Blank, with Matte White Cover

SLASXXX

**Product availability: Stock - Normally stocked in distribution facility**

### Main

Product or Component Type	Sensor
Type of Measurement	Temperature
Device Application	HVAC Temperature control
Flame Retardance	UL94-V0
IP Degree of Protection	IP20
Location	Living Space
Depth	0.9 in (24 mm)
Height	4.5 in (115 mm)
Width	3.3 in (85 mm)
Standards	UL 916 FCC Part 15 class B
Color	White
Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	0...95 %
Sensor Type	10 kOhm T3 thermistor
Surface Finish	Matte
Product name	SmartX Living Space Sensor
Range	SpaceLogic

### Complementary

Device presentation	Complete product
Connections - terminals	Screw - 2 AWG 24...AWG 18)
Range compatibility	EcoStruxure Building Operation SmartX Room Purpose Controller programmable controllers
Material	ABS (acrylonitrile butadiene-styrene)
Display type	Without Display
Communication port protocol	-- 2 wires

### Environment

Measurement range	0...50 °C temperature
-------------------	-----------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Product certifications</b>	CE conforming to EN 61000-6-3 RCM EAC ICES-003
-------------------------------	---

## Ordering and shipping details

<b>Category</b>	US1BMS180230
<b>Discount Schedule</b>	BMS1
<b>GTIN</b>	3606481817952
<b>Returnability</b>	Yes
<b>Country of origin</b>	MX

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	1.890 in (4.800 cm)
<b>Package 1 Width</b>	3.819 in (9.700 cm)
<b>Package 1 Length</b>	5.591 in (14.200 cm)
<b>Package 1 Weight</b>	4.868 oz (138.000 g)
<b>Unit Type of Package 2</b>	S03
<b>Number of Units in Package 2</b>	20
<b>Package 2 Height</b>	11.811 in (30.000 cm)
<b>Package 2 Width</b>	11.811 in (30.000 cm)
<b>Package 2 Length</b>	15.748 in (40.000 cm)
<b>Package 2 Weight</b>	7.161 lb(US) (3.248 kg)

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)