





	Description	Product Group	Quantity	Part No.	Part No.
Flowrite					
	Lower Seat Tools for Valve Size:	Flowrite			
	• 2-1/2"		1	599-09144	—
	• 3"		1	599-09145	—
	• 4"		1	599-09146	—
	• 5"		1	599-09147	—
	• 6"		1	599-09148	—
	Flowrite Union Kits.	Flowrite		Female	Male
	• 1/2" (15 mm)		1	599-09185	599-09181
	• 3/4" (20 mm)		1	599-09186	599-09182
	• 1" (25 mm)		1	599-09187	599-09183
	• 1-1/4" (32 mm)		1	599-09188	599-09184
	• 1-1/2" (40 mm)		1	599-09189	—
	• 2" (50 mm)		1	599-09190	—
	Flowrite Union Gasket Kits.	Flowrite			—
	• 1/2" NPT		25 Pieces	599-03394	—
	• 3/4" NPT		25 Pieces	599-03395	—
	• 1" NPT		25 Pieces	599-03396	—
	• 1-1/4" NPT		25 Pieces	599-03387	—
	• 1-1/2" NPT		25 Pieces	599-03388	—
	• 2" NPT		25 Pieces	599-03389	—
Magnetic					
	Control Signal Module w/ Feedback, 0-2".	MX..	1	ZM150	
	Control Signal Module w/ Feedback, 3-4".	MX..	1	ZM250	
	Terminal Housing. Converts 0 to 10 Vdc input to 0 to 20 Vdc phase cut output.				
	• up to 40W, IP30 rated housing	M3P	1	ZM100/A	
	• up to 40W, IP54 rated housing	M3P	1	ZM101/A	
	• up to 120W, IP30 rated housing	M3P	1	ZM200/A	
	Terminal Housing. For straight through 0 to 20 Vdc electrical housing only.				
	• to 40W, IP54 rated housing	M3P	1	ZM111	
	• up to 120W, IP30 rated housing	M3P	1	ZM210	
	Terminal Housing. Converts 0 to 20 mA/24 Vdc input to 0 to 20 Vdc phase cut output.				
	• up to 40W, IP30 rated housing	M3P	1	ZM120/A	
	• to 40W, IP54 rated housing	M3P	1	ZM121/A	
	• up to 120W, IP30 rated housing	M3P	1	ZM220/A	
	Blanking Flange.	M3P			
• 3"		1	Z155/80		
• 4"		1	Z155/100		