

Two-Way PICV Assemblies



ANSI Class 250
Electronic Non-Spring Return Actuators

- Normally Open or Closed
- Field adjustable maximum flow
- 100 psi close-off with ANSI Class IV leakage







NO/NC 1-1/2 to 2"			Non-Spring Return Actuator	
			Floating	0-10 V and 4-20 mA
2-Way Valve Body Part No.	Valve Size in.	Factory Preset Max. GPM	 SAY81.03U	 SAY61.03U
Normally Open or Closed (See Note Below)				
	1-1/2	15	334-04315-15	335-04315-15
		20	334-04315-20	335-04315-20
		25	334-04315-25	335-04315-25
		30	334-04315-30	335-04315-30
		35	334-04315-35	335-04315-35
		40	334-04315-40	335-04315-40
	2	20	334-04316-20	335-04316-20
		25	334-04316-25	335-04316-25
		30	334-04316-30	335-04316-30
		35	334-04316-35	335-04316-35
		40	334-04316-40	335-04316-40
		45	334-04316-45	335-04316-45
		50	334-04316-50	335-04316-50

Table Notes:

Part numbers in red indicate complete assemblies.

SAY actuators can be wired for normally closed operation.

0-10 V actuators require AZX61.1 Function Module, see technical instructions.

