

Two-Way PICV Assemblies



ANSI Class 250
Electronic Spring Return or Non-Spring Return Actuators

- Normally Closed
- Field adjustable maximum flow
- 45 psi close-off with ANSI Class IV leakage

PICV Selection Tables



NC 1/2 to 3/4"			Spring Return Actuator		Non-Spring Return Actuator	
			Floating	0-10 V	Floating	0-10 V
	Valve Size in.	Factory Preset Max. GPM				
			SSD81.5U	SSD61.5U	SSD81U	SSD61U
Normally Closed						
	1/2	0.5	232-04300-0.5	233-04300-0.5	230-04300-0.5	231-04300-0.5
		1.0	232-04300-1	233-04300-1	230-04300-1	231-04300-1
		1.5	232-04300-1.5	233-04300-1.5	230-04300-1.5	231-04300-1.5
		2.0	232-04300-2	233-04300-2	230-04300-2	231-04300-2
		2.5	232-04300-2.5	233-04300-2.5	230-04300-2.5	231-04300-2.5
		3.0	232-04301-3	233-04301-3	230-04301-3	231-04301-3
		3.5	232-04301-3.5	233-04301-3.5	230-04301-3.5	231-04301-3.5
		4.0	232-04301-4	233-04301-4	230-04301-4	231-04301-4
		4.5	232-04301-4.5	233-04301-4.5	230-04301-4.5	231-04301-4.5
		5.0	232-04301-5	233-04301-5	230-04301-5	231-04301-5
		5.5	232-04301-5.5	233-04301-5.5	230-04301-5.5	231-04301-5.5
		6.0	232-04301-6	233-04301-6	230-04301-6	231-04301-6
		6.5	232-04301-6.5	233-04301-6.5	230-04301-6.5	231-04301-6.5
		7.0	232-04301-7	233-04301-7	230-04301-7	231-04301-7
		7.5	232-04301-7.5	233-04301-7.5	230-04301-7.5	231-04301-7.5
	3/4	1.0	232-04302-1	233-04302-1	230-04302-1	231-04302-1
		1.5	232-04302-1.5	233-04302-1.5	230-04302-1.5	231-04302-1.5
		2.0	232-04302-2	233-04302-2	230-04302-2	231-04302-2
		2.5	232-04302-2.5	233-04302-2.5	230-04302-2.5	231-04302-2.5
		3.0	232-04302-3	233-04302-3	230-04302-3	231-04302-3
		3.5	232-04302-3.5	233-04302-3.5	230-04302-3.5	231-04302-3.5
		4.0	232-04302-4	233-04302-4	230-04302-4	231-04302-4
		4.5	232-04302-4.5	233-04302-4.5	230-04302-4.5	231-04302-4.5
		5.0	232-04303-5	233-04303-5	230-04303-5	231-04303-5
		5.5	232-04303-5.5	233-04303-5.5	230-04303-5.5	231-04303-5.5
		6.0	232-04303-6	233-04303-6	230-04303-6	231-04303-6
		6.5	232-04303-6.5	233-04303-6.5	230-04303-6.5	231-04303-6.5
		7.0	232-04303-7	233-04303-7	230-04303-7	231-04303-7
		7.5	232-04303-7.5	233-04303-7.5	230-04303-7.5	231-04303-7.5
		8.0	232-04303-8	233-04303-8	230-04303-8	231-04303-8
8.5	232-04303-8.5	233-04303-8.5	230-04303-8.5	231-04303-8.5		

Table Notes:
Part numbers in red indicate complete assemblies.

A-17

Valves