

Two-Way Flanged PICV Assemblies

NEW!

ANSI Class 125 and 250

Electronic Spring Return or Non-Spring Return Actuators

- Normally Open or Normally Closed
- Field adjustable maximum flow
- 100 psi close-off with ANSI Class IV leakage









NO/NC 2-1/2 to 3"			Spring Return Actuator		Non-Spring Return Actuator	
			NO	NC	NO	
			Floating, 0-10 V, 4 to 20 mA		Floating	0-10 V
2-Way Valve Body Part No.	Valve Size in.	Maximum Flow	 SQV91P30U	 SQV91P40U	 SAX81.03U	 SAX61.03U
ANSI CLASS 125						
 599-07310	2-1/2	110	238-07310	239-07310	373-07310	371-07310
599-07315		154	238-07315	239-07315	373-07315	371-07315
599-07311	3	150	238-07311	239-07311	373-07311	371-07311
599-07316		190	238-07316	239-07316	373-07316	371-07316
ANSI CLASS 250						
 599-07320	2-1/2	110	238-07320	239-07320	373-07320	371-07320
599-07325		154	238-07325	239-07325	373-07325	371-07325
599-07321	3	150	238-07321	239-07321	373-07321	371-07321
599-07326		190	238-07326	239-07326	373-07326	371-07326

Table Notes:

Part numbers in red indicate complete assemblies.

A-20

Valves