

Two-Way **Globe** Valve Assemblies — MT Series

ANSI Class 250

Pneumatic Spring Return Actuators

- Normally Open or Normally Closed
- Brass and Stainless Steel Trim








NO/NC 1/2 to 1"			Spring Return Actuator		
			3-8 psi (21-55 kPa)	8-13 psi (55-90 kPa)	10-15 psi (69-103 kPa)
2-Way Valve Body Part No.	Valve Size in.	Flow Rate Cv			
			599-01088	599-01088	599-01088
Normally Open					
			Close-off psi — Brass Trim		
599-02030	1/2	0.4	95 257-02030	45 258-02030C	20 256-02030A
599-02032		0.63	95 257-02032	45 258-02032C	20 256-02032A
599-02034		1	95 257-02034	45 258-02034C	20 256-02034A
599-02036		1.6	95 257-02036	45 258-02036C	20 256-02036A
599-02038		2.5	45 257-02038	25 258-02038C	15 256-02038A
599-02041		4	45 257-02041	25 258-02041C	15 256-02041A
599-02044	3/4	6.3	35 257-02044	10 258-02044C	—
599-02046	1	10	35 257-02046	10 258-02046C	—
			Close-off psi — Stainless Steel Trim		
599-02047	1/2	0.4	95 257-02047	45 258-02047C	20 256-02047A
599-02049		0.63	95 257-02049	45 258-02049C	20 256-02049A
599-02051		1	95 257-02051	45 258-02051C	20 256-02051A
599-02053		1.6	95 257-02053	45 258-02053C	20 256-02053A
599-02055		2.5	45 257-02055	25 258-02055C	15 256-02055A
599-02058		4	45 257-02058	25 258-02058C	15 256-02058A
599-02061	3/4	6.3	35 257-02061	10 258-02061C	—
599-02063	1	10	35 257-02063	10 258-02063C	—
Normally Closed					
			Close-off psi — Brass Trim		
599-02000	1/2	0.4	40 257-02000B	95 258-02000C	95 256-02000
599-02002		0.63	40 257-02002B	95 258-02002C	95 256-02002
599-02004		1	40 257-02004B	95 258-02004C	95 256-02004
599-02006		1.6	40 257-02006B	95 258-02006C	95 256-02006
599-02008		2.5	28 257-02008B	50 258-02008C	50 256-02008
599-02010		4	28 257-02010B	50 258-02010C	50 256-02010
599-02012	3/4	6.3	18 257-02012B	40 258-02012C	40 256-02012
599-02014	1	10	18 257-02014B	40 258-02014C	40 256-02014
			Close-off psi — Stainless Steel Trim		
599-02015	1/2	0.4	40 257-02015B	95 258-02015C	95 256-02015
599-02017		0.63	40 257-02017B	95 258-02017C	95 256-02017
599-02019		1	40 257-02019B	95 258-02019C	95 256-02019
599-02021		1.6	40 257-02021B	95 258-02021C	95 256-02021
599-02023		2.5	28 257-02023B	50 258-02023C	50 256-02023
599-02025		4	28 257-02025B	50 258-02025C	50 256-02025
599-02027	3/4	6.3	18 257-02027B	40 258-02027C	40 256-02027
599-02029	1	10	18 257-02029B	40 258-02029C	40 256-02029

Table Notes:

Part numbers in red indicate complete assemblies. Black numbers indicate close-off psi.

Normally Open Values in chart are for 20 psi supplied to the actuator.

Normally Closed Values in chart are for 0 psi supplied to the actuator.