

Three-Way **Globe** Valve Assemblies — MT Series

ANSI Class 250

Electronic Spring Return or Non-Spring Return Actuators

- Brass and Stainless Steel Trim



Mixing 1/2 to 1"				Spring Return Actuator				Non-Spring Return Actuator		
				Floating		0-10 V		Floating	0-10 V	
3-Way Valve Body Part No.	Valve Size in.	Flow Rate Cv	Close Off psi							
				Brass Trim						
599-02064	1/2	0.4	95	260-02064	266-02064	262-02064	265-02064	259-02064	261-02064	264-02064
599-02065		0.63	95	260-02065	266-02065	262-02065	265-02065	259-02065	261-02065	264-02065
599-02066		1	95	260-02066	266-02066	262-02066	265-02066	259-02066	261-02066	264-02066
599-02067		1.6	95	260-02067	266-02067	262-02067	265-02067	259-02067	261-02067	264-02067
599-02068		2.5	50	260-02068	266-02068	262-02068	265-02068	259-02068	261-02068	264-02068
599-02069		4	50	260-02069	266-02069	262-02069	265-02069	259-02069	261-02069	264-02069
599-02070	3/4	6.3	40	260-02070	266-02070	262-02070	265-02070	259-02070	261-02070	264-02070
599-02071	1	10	40	260-02071	266-02071	262-02071	265-02071	259-02071	261-02071	264-02071
				Stainless Steel Trim						
599-02072	1/2	0.4	95	260-02072	266-02072	262-02072	265-02072	259-02072	261-02072	264-02072
599-02073		0.63	95	260-02073	266-02073	262-02073	265-02073	259-02073	261-02073	264-02073
599-02074		1	95	260-02074	266-02074	262-02074	265-02074	259-02074	261-02074	264-02074
599-02075		1.6	95	260-02075	266-02075	262-02075	265-02075	259-02075	261-02075	264-02075
599-02076		2.5	50	260-02076	266-02076	262-02076	265-02076	259-02076	261-02076	264-02076
599-02077		4	50	260-02077	266-02077	262-02077	265-02077	259-02077	261-02077	264-02077
599-02078	3/4	6.3	40	260-02078	266-02078	262-02078	265-02078	259-02078	261-02078	264-02078
599-02079	1	10	40	260-02079	266-02079	262-02079	265-02079	259-02079	261-02079	264-02079

Table Notes:

Part numbers in red indicate complete assemblies. Black numbers indicate close-off psi.

Values are for the NC upper port. For NO lower port values, refer to Engineering, Section G.

A-28

Valves

