









## Two-Way Flanged **Globe** Valve Assemblies

ANSI Class 250

Electronic Spring Return Actuators

- Normally Open or Normally Closed
- Equal Percentage
- Bronze and Stainless Steel Trim



NO/NC Equal Percentage Flanged 2-1/2 to 6"			Spring Return Actuator					
			Floating 3P	Floating 3P	Floating 3P	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA
2-Way Valve Body Part No.	Valve Size in.	Flow Rate Cv						
			SKD82.51U	SKB82.51U	SKC82.61U	SKD62U	SKB62U	SKC62U
<b>Normally Open</b>			<b>Close-off psi — Bronze Trim</b>					
	599-05940	2-1/2 63	38 <b>276-05940</b>	153 <b>289-05940</b>	—	38 <b>274-05940</b>	153 <b>291-05940</b>	—
	599-05941	3 100	25 <b>276-05941</b>	101 <b>289-05941</b>	—	25 <b>274-05941</b>	101 <b>291-05941</b>	—
	599-05942	4 160	—	—	65 <b>292-05942</b>	—	—	65 <b>294-05942</b>
	599-05943	5 250	—	—	42 <b>292-05943</b>	—	—	42 <b>294-05943</b>
	599-05944	6 400	—	—	29 <b>292-05944</b>	—	—	29 <b>294-05944</b>
			<b>Close-off psi — Stainless Steel Trim</b>					
	599-05920	2-1/2 63	38 <b>276-05920</b>	153 <b>289-05920</b>	—	38 <b>274-05920</b>	153 <b>291-05920</b>	—
	599-05921	3 100	25 <b>276-05921</b>	101 <b>289-05921</b>	—	25 <b>274-05921</b>	101 <b>291-05921</b>	—
	599-05922	4 160	—	—	65 <b>292-05922</b>	—	—	65 <b>294-05922</b>
	599-05923	5 250	—	—	42 <b>292-05923</b>	—	—	42 <b>294-05923</b>
	599-05924	6 400	—	—	29 <b>292-05924</b>	—	—	29 <b>294-05924</b>
<b>Normally Closed</b>			<b>Close-off psi — Bronze Trim</b>					
	599-05950	2-1/2 63	34 <b>276-05950</b>	97 <b>289-05950</b>	—	34 <b>274-05950</b>	97 <b>291-05950</b>	—
	599-05951	3 100	22 <b>276-05951</b>	63 <b>289-05951</b>	—	22 <b>274-05951</b>	63 <b>291-05951</b>	—
	599-05952	4 160	—	—	39 <b>292-05952</b>	—	—	39 <b>294-05952</b>
	599-05953	5 250	—	—	25 <b>292-05953</b>	—	—	25 <b>294-05953</b>
	599-05954	6 400	—	—	17 <b>292-05954</b>	—	—	17 <b>294-05954</b>
			<b>Close-off psi — Stainless Steel Trim</b>					
	599-05930	2-1/2 63	34 <b>276-05930</b>	97 <b>289-05930</b>	—	34 <b>274-05930</b>	97 <b>291-05930</b>	—
	599-05931	3 100	22 <b>276-05931</b>	63 <b>289-05931</b>	—	22 <b>274-05931</b>	63 <b>291-05931</b>	—
	599-05932	4 160	—	—	39 <b>292-05932</b>	—	—	39 <b>294-05932</b>
	599-05933	5 250	—	—	25 <b>292-05933</b>	—	—	25 <b>294-05933</b>
	599-05934	6 400	—	—	17 <b>292-05934</b>	—	—	17 <b>294-05934</b>

**Table Notes:**

Part numbers in red indicate complete assemblies. Black numbers indicate close-off psi.

A-49

Valves