

Two-Way Flanged **Globe** Valve Assemblies

ANSI Class 125
Electronic Spring Return Actuators

- Normally Open or Normally Closed
- Linear
- Stainless Steel Trim



A-42

Valves

NO/NC Linear Flanged 2-1/2 to 6"			Spring Return Actuator								
			Floating 3P	Floating 3P	Floating 3P	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA			
2-Way Valve Body Part No.	Valve Size in.	Flow Rate Cv									
			SKD82.51U	SKB82.51U	SKC82.61U	SKD62U	SKB62U	SKC62U			
Normally Open			Close-off psi — Standard-temperature Range 20° F to 250° F (-7° C to 120° C)								
	599-06060	2-1/2 63	38 276-06060	153 289-06060	—	38 274-06060	153 291-06060	—			
	599-06061	3 100	25 276-06061	101 289-06061	—	25 274-06061	101 291-06061	—			
	599-06062	4 160	—	—	65 292-06062	—	—	65 294-06062			
	599-06063	5 250	—	—	42 292-06063	—	—	42 294-06063			
	599-06064	6 400	—	—	29 292-06064	—	—	29 294-06064			
			Close-off psi — High-temperature Range is 337° F max. (170° C)								
	599-06040	2-1/2 63	38 276-06040	153 289-06040	—	38 274-06040	153 291-06040	—			
	599-06041	3 100	25 276-06041	101 289-06041	—	25 274-06041	101 291-06041	—			
	599-06042	4 160	—	—	65 292-06042	—	—	65 294-06042			
	599-06043	5 250	—	—	42 292-06043	—	—	42 294-06043			
	599-06044	6 400	—	—	29 292-06044	—	—	29 294-06044			
Normally Closed			Close-off psi — Standard-temperature Range 20° F to 250° F (-7° C to 120° C)								
	599-06070	2-1/2 63	34 276-06070	97 289-06070	—	34 274-06070	97 291-06070	—			
	599-06071	3 100	22 276-06071	63 289-06071	—	22 274-06071	63 291-06071	—			
	599-06072	4 160	—	—	39 292-06072	—	—	39 294-06072			
	599-06073	5 250	—	—	25 292-06073	—	—	25 294-06073			
	599-06074	6 400	—	—	17 292-06074	—	—	17 294-06074			
			Close-off psi — High-temperature Range is 337° F max. (170° C)								
	599-06050	2-1/2 63	34 276-06050	97 289-06050	—	34 274-06050	97 291-06050	—			
	599-06051	3 100	22 276-06051	63 289-06051	—	22 274-06051	63 291-06051	—			
	599-06052	4 160	—	—	39 292-06052	—	—	39 294-06052			
	599-06053	5 250	—	—	25 292-06053	—	—	25 294-06053			
	599-06054	6 400	—	—	17 292-06054	—	—	17 294-06054			

Table Notes:
Part numbers in red indicate complete assemblies. Black numbers indicate close-off psi.