

# Two-Way Flanged **Globe** Valve Assemblies









ANSI Class 250  
Electronic Spring Return Actuators

- Normally Open or Normally Closed
- Linear
- Stainless Steel Trim



A-52

Valves

NO/NC Linear Flanged 2-1/2 to 6"			Spring Return Actuator					
			Floating 3P	Floating 3P	Floating 3P	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA	0-10 Vdc 4-20 mA
2-Way Valve Body Part No.	Valve Size in.	Flow Rate Cv						
			SKD82.51U	SKB82.51U	SKC82.61U	SKD62U	SKB62U	SKC62U
<b>Normally Open</b>			<b>Close-off psi — Standard-temperature Range 20° F to 250° F (-7° C to 120° C)</b>					
	599-06140	2-1/2 63	38 <b>276-06140</b>	153 <b>289-06140</b>	—	38 <b>274-06140</b>	153 <b>291-06140</b>	—
	599-06141	3 100	25 <b>276-06141</b>	101 <b>289-06141</b>	—	25 <b>274-06141</b>	101 <b>291-06141</b>	—
	599-06142	4 160	—	—	65 <b>292-06142</b>	—	—	65 <b>294-06142</b>
	599-06143	5 250	—	—	42 <b>292-06143</b>	—	—	42 <b>294-06143</b>
	599-06144	6 400	—	—	29 <b>292-06144</b>	—	—	29 <b>294-06144</b>
			<b>Close-off psi — High-temperature Range is 337° F max. (170° C)</b>					
	599-06120	2-1/2 63	38 <b>276-06120</b>	153 <b>289-06120</b>	—	38 <b>274-06120</b>	153 <b>291-06120</b>	—
	599-06121	3 100	25 <b>276-06121</b>	101 <b>289-06121</b>	—	25 <b>274-06121</b>	101 <b>291-06121</b>	—
	599-06122	4 160	—	—	65 <b>292-06122</b>	—	—	65 <b>294-06122</b>
	599-06123	5 250	—	—	42 <b>292-06123</b>	—	—	42 <b>294-06123</b>
	599-06124	6 400	—	—	29 <b>292-06124</b>	—	—	29 <b>294-06124</b>
<b>Normally Closed</b>			<b>Close-off psi — Standard-temperature Range 20° F to 250° F (-7° C to 120° C)</b>					
	599-06150	2-1/2 63	34 <b>276-06150</b>	97 <b>289-06150</b>	—	34 <b>274-06150</b>	97 <b>291-06150</b>	—
	599-06151	3 100	22 <b>276-06151</b>	63 <b>289-06151</b>	—	22 <b>274-06151</b>	63 <b>291-06151</b>	—
	599-06152	4 160	—	—	39 <b>292-06152</b>	—	—	39 <b>294-06152</b>
	599-06153	5 250	—	—	25 <b>292-06153</b>	—	—	25 <b>294-06153</b>
	599-06154	6 400	—	—	17 <b>292-06154</b>	—	—	17 <b>294-06154</b>
			<b>Close-off psi — High-temperature Range is 337° F max. (170° C)</b>					
	599-06130	2-1/2 63	34 <b>276-06130</b>	97 <b>289-06130</b>	—	34 <b>274-06130</b>	97 <b>291-06130</b>	—
	599-06131	3 100	22 <b>276-06131</b>	63 <b>289-06131</b>	—	22 <b>274-06131</b>	63 <b>291-06131</b>	—
	599-06132	4 160	—	—	39 <b>292-06132</b>	—	—	39 <b>294-06132</b>
	599-06133	5 250	—	—	25 <b>292-06133</b>	—	—	25 <b>294-06133</b>
	599-06134	6 400	—	—	17 <b>292-06134</b>	—	—	17 <b>294-06134</b>

**Table Notes:**  
Part numbers in red indicate complete assemblies. Black numbers indicate close-off psi.