

References

UL98 Non Fusible Disconnect switches

Rating (A)	No. of poles	Switch body	Direct handle	External front and right side handles	Shafts for external front and side handles	Switched fourth pole module	Unswitched neutral pole	Earth module	Auxiliary contacts	Terminal shrouds
30 A	3 P	2201 3003	Blue 2299 5032	S00 type I - 0 Black 4, 4X 147D 1111	150 mm 5.9 in 1407 0515 200 mm 7.9 in 1407 0520 320 mm 12.6 in 1407 0532 ⁽¹⁾	1 P 2201 1003	1 P 2200 5011 ⁽²⁾	1 P 2200 9011 ⁽²⁾	M type 1 AC NO + NC 2299 0001 M type 1 AC 2 NC 2299 0011	1 P 2294 1011 ⁽³⁾ 3 P 2294 3016 ⁽³⁾
60 A	3 P	2201 3006		Red/Yellow 4, 4X 147E 1111		1 P 2201 1006				
100 A	3 P	2200 3010		S0 type I - 0 Black 4, 4X 148D 1111 Red/Yellow 4, 4X 148E 1111		1 P 2200 1010				

(1) Shaft guide reference 14190000, is required for shaft length over 15.7 inches (400 mm).

(2) Not UL.

(3) Top and bottom.