

References

BS88 - Front and side operation - Switch body with a shunt trip coil - 230 VAC

Rating (A) Fuse ⁽¹⁾	No. of poles	Front operation Switch body	Side operation Switch body	Direct handle ⁽²⁾	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	Terminal shrouds ⁽³⁾	Terminal screens ⁽⁴⁾	Inter phase barrier
250 A B1-B2-B3	3 P	3660 3026	3665 3026	Front operation Black 3999 6201	S3 type	Front operation 200 mm 1401 1520 320 mm 1401 1532 ⁽²⁾	1 st contact NO/NC 3999 0051 2 nd contact NO/NC 3999 0052	1 contact NO/NC 3999 0031	3 P 3998 3040 4 P 3998 4040		
	4 P	3660 6026	3665 6026								
400 A B1-B2- B3-B4	3 P	3660 3041	3665 3041	Side operation Black 3999 6012	Front operation Black IP55 1431 3511 ⁽²⁾ Red IP55 1432 3511	Side operation 200 mm 1403 1520			3998 3063		
	4 P	3660 6041	3665 6041								
630 A C1-C2	3 P	3660 3064	3665 3064	Front operation Black 3999 6012	Side operation Black IP55 1435 3511 ⁽²⁾ Red IP55 1436 3511				3998 4063		
	4 P	3660 6064	3665 6064								
800 A C1-C2-C3	3 P	3660 3080	3665 3080	Side operation Black 3999 6012					3 P 3998 3120 4 P 3998 4120	3 P 2998 0003 4 P 2998 0004	
	4 P	3660 6080	3665 6080								
1250 A D1	3 P	3660 3121	3665 3121								
	4 P	3660 6121	3665 6121								

(1) For the fuses: see page 230 "BS88 industrial fuselinks".

(2) Standard.

(3) Top/bottom.

(4) Bottom terminals protection screen as standard.

FUSOMAT

Visible breaking and tripping fuse switches
from 250 to 1250 A

References

NFC and DIN - Front operation - Switch body with a shunt trip coil - 230 VAC

Rating (A) Fuse	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	1 st Fuse blown AC	Terminal shrouds (1 piece)	Terminal screens top	Inter phase barrier																				
250 A / 1	3 P	3650 3026	Black 3999 6201⁽¹⁾	S3 type Black IP55 1431 3511⁽¹⁾ S3 type Red/yellow IP55 1432 3511	200 mm 1401 1520 320 mm 1401 1532⁽¹⁾	1 st contact NO/NC 3999 0051 2 nd contact NO/NC 3999 0052	1 contact NO/NC 3999 0031	3 P 3994 1304	3 P 3998 3040⁽²⁾																						
	4 P	3650 6026						4 P 3994 1404	4 P 3998 4040⁽²⁾																						
400 A / 2	3 P	3650 3041						3 P 3994 1306	3 P 3998 3063⁽²⁾																						
	4 P	3650 6041						4 P 3994 1406	4 P 3998 4063⁽²⁾																						
630 A / 3	3 P	3650 3064						3 P 3994 1312	3 P 3998 3120⁽³⁾			3 P 2998 0003																			
	4 P	3650 6064						4 P 3994 1412	4 P 3998 4120⁽³⁾			4 P 2998 0004																			
800 A / 4	3 P	3650 3080	Black 3999 6012⁽¹⁾									3 P 3994 1312		3 P 3998 3120⁽³⁾	3 P 2998 0003																
	4 P	3650 6080																													
1250 A / 4	3 P	3650 3121																													
	4 P	3650 6121																													

(1) Standard.

(2) Top/bottom.

(3) Bottom terminals protection screen as standard.

NFC and DIN - Side operation - Switch body with a shunt trip coil - 230 VAC

Rating (A) Fuse	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	1 st Fuse blown AC	Terminal shrouds (1 piece)	Terminal screens top	Inter phase barrier		
250 A / 1	3 P	3655 3026	Black 3999 6012⁽¹⁾	S3 type Black IP55 1435 3511⁽¹⁾ S3 type Red IP55 1436 3511	200 mm 1403 1520	1 st contact NO/NC 3999 0051 2 nd contact NO/NC 3999 0052	1 contact NO/NC 3999 0031	3 P 3994 1304	3 P 3998 3040⁽²⁾				
	4 P	3655 6026											
400 A / 2	3 P	3655 3041						4 P 3994 1404	4 P 3998 4040⁽²⁾				
	4 P	3655 6041											
630 A / 3	3 P	3655 3064						3994 1306	3998 3063⁽²⁾				
	4 P	3655 6064											
800 A / 4	3 P	3655 3080						3 P 3994 1312	3 P 3998 3120⁽³⁾	3 P 2998 0003	3 P 2998 0003		
	4 P	3655 6080											
1250 A / 4	3 P	3655 3121						4 P 3994 1412	4 P 3998 4120⁽³⁾	4 P 2998 0004	4 P 2998 0004		
	4 P	3655 6121											

(1) Standard.

(2) Top/bottom.

(3) Bottom terminals protection screen as standard.