


Product data sheet

Characteristics

10287

Multi9 - comb busbar - 3L - 18 mm pitch - 12 modules - 100A

Product availability : Stock - Normally stocked in distribution facility



Main

Range	Multi 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L
Length in 18 mm modules	12

Complementary

Number of ways	4 ways 3 L
Poles configuration for 1 way	1 x 3P
Connection pitch	0.71 in (18 mm)
Connector type	Tooth
Distance between way	2.13 in (54 mm)
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Uncuttable
[Ie] rated operational current	100 A 104 °F (40 °C)
[Ue] rated operational voltage	277 V AC Ph/N 480 V AC Ph/Ph
[Ui] rated insulation voltage	690 V AC
[Uimp] rated impulse withstand voltage	12 kV
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	8.50 in (216 mm)
Color	Light gray RAL 7035)
Range compatibility	Multi 9 C60SP

Environment

Standards	IEC 60947-2
-----------	-------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Jun 11, 2021

GB 14048.2
UL 1077

Fire resistance	1760 °F (960 °C) 30 s)
-----------------	-------------------------

Ordering and shipping details

Category	00908 - C60N SUPPLEMENTARY PROTECTORS
Discount Schedule	DE2
GTIN	00785901860679
Nbr. of units in pkg.	1
Package weight(Lbs)	0.24 lb(US) (0.11 kg)
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.51 in (1.3 cm)
Package 1 width	2.17 in (5.5 cm)
Package 1 Length	8.66 in (22 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	144
Package 2 Weight	35.36 lb(US) (16.039 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------