

Product data sheet

Characteristics

2510MBW12V06P11

Manual Starter, integral horsepower, NEMA M0, 600VAC, 3 pole, 5 HP at 380/575VAC, three phase, red indicator, NEMA 4/4X

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	Red indicator, 480 V
Horsepower Rating	3 hp 200...230 V AC, 3 phase 5 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	10.92 in (277.37 mm)
Width	5.78 in (146.81 mm)
Depth	5.76 in (146.30 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
----------------	---

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

NEMA Enclosure Rating	NEMA 4/4X brushed stainless steel
-----------------------	-----------------------------------

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Package weight(Lbs)	9.28 lb(US) (4.21 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------