

Product data sheet

Characteristics

2601BW1

Switch, reversing drum, 5 HP at 575 VAC single phase, 7.5 HP at 575 VAC polyphase, handle operated, NEMA 4 enclosure

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product	Reversing Drum Switch
Enclosure Rating	NEMA 4
Horsepower	1.5 hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase 5 hp 460 V AC, 1 phase 5 hp 575 V AC, 1 phase 5 hp 200 V AC, 3 phase 5 hp 230 V AC, 3 phase 7.5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase 2 hp 115 V DC 2 hp 230 V DC
Maximum Rated Voltage	600 V AC 250 V DC
Number of Poles	3P

Complementary

Certifications	CSA UL Listed
Electrical Connection	Screw-clamp terminals
Type	B
Width	4.40 in (111.76 mm)
Height	6.89 in (175.01 mm)
Depth	5.50 in (139.70 mm)

Ordering and shipping details

Category	21116 - 2601
----------	--------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	CP1
GTIN	00785901784449
Nbr. of units in pkg.	1
Package weight(Lbs)	3.53 lb(US) (1.60 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	4.80 in (12.192 cm)
Package 1 width	5.00 in (12.700 cm)
Package 1 Length	8.00 in (20.320 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------