

# Product data sheet

## Characteristics

# 3104140042

NEMA Motor Starter, Type S, replacement coil, 110/120 VAC 50/60 Hz, NEMA Size 00, 0 and 1 starters and 8903SM lighting

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Coil
Accessory / separate part destination	Class 8502 type SA (series A)/SB/SC contactor Class 8536 type SA (series A)/SB/SC starter Class 8903 type SM lighting contactor

### Complementary

NEMA size	1 00 0
[Ue] rated operational voltage	120 V AC 60 Hz 110 V AC 50 Hz
Inrush power in VA	245 VA 232 VA
Average consumption	27 VA 26 VA
Height	2.15 in (54.7 mm)
Width	3.21 in (81.5 mm)
Depth	1.90 in (48.3 mm)

### Ordering and shipping details

Category	18079 - SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
GTIN	00785901229124
Package weight(Lbs)	0.46 lb(US) (0.21 kg)
Returnability	Yes

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Country of origin	MX
-------------------	----

---

**Offer Sustainability**

---

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---