

Product data sheet

Characteristics

3104140048

NEMA Motor Starter, Type S, replacement coil, 208 VAC 60 Hz, NEMA Size 00, 0 and 1 starters and 8903SM lighting

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Coil
Accessory / separate part destination	Class 8502 type SA (series A)/SB/SC contactor Class 8536 type SA (series A)/SB/SC starter Class 8903 type SM lighting contactor

Complementary

NEMA size	0 00 1
[Ue] rated operational voltage	208 V AC 60 Hz
Inrush power in VA	245 VA
Average consumption	27 VA
Height	2.15 in (54.7 mm)
Width	3.21 in (81.5 mm)
Depth	1.90 in (48.3 mm)

Ordering and shipping details

Category	18079 - SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
GTIN	00785901107378
Package weight(Lbs)	0.44 lb(US) (0.20 kg)
Returnability	Yes
Country of origin	MX

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
