

Product data sheet

Characteristics

500SV43B

TRANSFORMER DRY 1P .5KVA

120X240V-12/24V

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Buck and Boost Transformer
Enclosure Code	5A
Enclosure Type	NEMA 3R
Insulation Temperature	266 °F (130 °C)
Primary Voltage	120 x 240 V
Power Rating	0.5 kVA
Secondary Voltage	12/24 V
Temperature Rise	80 °C

Complementary

Height	6.18 in (157 mm)
Width	6.18 in (157 mm)
Depth	4.53 in (115 mm)
Net Weight	13.8 lb(US) (6.26 kg) 13.80 lb(US) (6.26 kg)

Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901876199
Nbr. of units in pkg.	1
Package weight(Lbs)	15.55 lb(US) (7.05 kg)
Returnability	Yes
Country of origin	MX

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Package 1 Height	7.20 in (18.288 cm)
Package 1 width	8.30 in (21.082 cm)
Package 1 Length	8.80 in (22.352 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------