



Main

Product range	8501N
Product type	Relay Socket
Pin shape	Spade
Number of pins	8
[In] rated current	10 A 300 V AC

Complementary

Electrical connection	Double tiered screw clamp terminals
Mounting type	Panel DIN rail
Package quantity	1

Environment

Certifications	UL Recognized CSA RoHS CE
Maximum Height	2.72 in (69.09 mm)
Width	1.18 in (29.92 mm)
Depth	0.99 in (25.27 mm)

Ordering and shipping details

Category	21142 - 8501 N
Discount Schedule	CP2
GTIN	00785901097846
Nbr. of units in pkg.	1

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package weight(Lbs)	0.11 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	1.20 in (3.048 cm)
Package 1 width	2.90 in (7.366 cm)
Package 1 Length	1.30 in (3.302 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds and Di-isodecyl phthalate (DIDP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------