

# Product data sheet

## Characteristics

# 8501NR61

Plug in relay, Type N, relay socket, 11 tubular pin, single tier, for 8510KP relays and 9050JCK timers

Product availability : Stock - Normally stocked in distribution facility



### Main

Product range	8501N
Product type	Relay Socket
Pin shape	Tubular
Number of pins	11
[In] rated current	15 A 300 V AC 5 A 600 V AC

### Complementary

Electrical connection	Single tiered screw clamp terminals
Mounting type	Panel DIN rail
Package quantity	1

### Environment

Certifications	UL Recognized CSA CE
Height	2.16 in (54.8 mm)
Width	2.32 in (59 mm)
Depth	0.97 in (24.6 mm)

### Ordering and shipping details

Category	21142 - 8501 N
Discount Schedule	CP2
GTIN	00785901583677

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.	1
Package weight(Lbs)	0.14 lb(US) (0.06 kg)
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.10 in (2.794 cm)
Package 1 width	2.40 in (6.096 cm)
Package 1 Length	2.30 in (5.842 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------