

Product data sheet

Characteristics

8501RS42V20

Plug in relay, Type R, miniature, 1 HP at 277 VAC, 15A resistive at 120 VAC, 8 blade, DPDT, 2 NO, 2 NC, 120 VAC coil

Product availability : Stock - Normally stocked in distribution facility



Main

Product range	8501R
Product type	Miniature Relay
Relay type	Standard

Complementary

Mounting type	Socket
Contact composition	DPDT
[Uc] control circuit voltage	120 V AC
Pilot light	No indicator
Manual operator	Without test button
Horsepower rating	0.5 120 V AC 1 277 V AC
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 15 A 28 V DC resistive control circuit UL 508
Maximum switching voltage	300 V AC 30 V DC
Contact material	Silver alloy, gold flashed
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR42
Height	1.07 in (27.3 mm)
Width	0.83 in (21 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	1.65 in (41.8 mm)
-------	-------------------

Environment

Ambient temperature range - operational	-40...131 °F (-40...55 °C)
Product certifications	UL Listed UL Recognized CSA CE

Ordering and shipping details

Category	21143 - 8501 R
Discount Schedule	CP2
GTIN	00785901131311
Nbr. of units in pkg.	1
Package weight(Lbs)	0.09 lb(US) (0.04 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	1.30 in (3.302 cm)
Package 1 width	1.40 in (3.556 cm)
Package 1 Length	2.00 in (5.080 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------