

Product data sheet

Characteristics

8502SCO2V02S

NEMA Contactor, Type S, nonreversing, Size 1, 27A, 10 HP at 575 VAC, 3 phase, up to 100 kA, 3 pole, 120 VAC coil, open

Product availability : Stock - Normally stocked in distribution facility



Main

Product Type	Contacteur
Type	8502S
Control Circuit Type	Separate control circuit
Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Contacteur Type	Non-reversing
Current Rating	27 A
Number of Poles	3P
Phase	3 phase
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Maximum Voltage Rating	600 V AC
SCCR	Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	Fuse not supplied
Electrical Connection	Screw clamp terminals
Enclosure Type	Not rated (open device)
Certifications	UL listed file E78351 CCN NLDX CSA

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

NEMA Size	1
Height	4.34 in (110.24 mm)
Depth	4.22 in (107.19 mm)
Width	3.22 in (81.79 mm)

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901862901
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3 lb(US) (1.50 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.50 in (11.43 cm)
Package 1 width	5.80 in (14.732 cm)
Package 1 Length	8.00 in (20.32 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------