

Product data sheet

Characteristics

8536SAG12V08H30

Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR, NEMA 1 +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phase
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	00
Height	10.00 in (254 mm)
Depth	5.55 in (141 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product certifications	CSA UL Listed NEMA
------------------------	--------------------------

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901786603
Package weight(Lbs)	8 lb(US) (3.63 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------