

# Product data sheet

## Characteristics

# 8536SDG1V08H30

NEMA Motor Starter, Type S, nonreversing, Size 2, 45A, 25 HP at 460 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic, 208 VAC coil, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

### Complementary

NEMA Size	2
Rated Current	45 A
Number of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Solid state Motor Logic class 10/20
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
SCCR	Circuit-breaker 100 A maximum: 100 kA at 480 V AC Fuse J 100 A maximum: 100 kA at 600 V AC Fuse T 100 A maximum: 100 kA at 600 V AC Fuse RK1 100 A maximum: 100 kA at 600 V AC Fuse RK5 100 A maximum: 100 kA at 600 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	12.69 in (322.33 mm)
Width	7.81 in (198.37 mm)
Depth	6.31 in (160.27 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA NEMA

## Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901986904
Nbr. of units in pkg.	1
Package weight(Lbs)	13.77 lb(US) (6.25 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	7.80 in (19.812 cm)
Package 1 width	8.40 in (21.336 cm)
Package 1 Length	13.00 in (33.020 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------