

Product data sheet

Characteristics

8538SBA23V81CFF4P1TX11

NEMA Combination Starter, Type S, 30A fusible disconnect, Size 0, 18A, 5 HP at 600 VAC polyphase, 120 VAC coil, NEMA 12

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
NEMA size	0

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45 lb(US) (20.41 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------