

Product data sheet

Characteristics

8538SCG11V02S

NEMA Combination Starter, Type S, nonfusible disconnect, Size 1, 27A, 10 HP at 600 VAC polyphase, 120 VAC coil, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5 hp 200 V AC, 3 phase 7.5 hp 230 V AC, 3 phase 10 hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Non-fusible disconnect switch
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901744368
Package weight(Lbs)	34.35 lb(US) (15.58 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------