

# Product data sheet

## Characteristics

# 8538SCG13V02S

NEMA Combination Starter, Type S, 60A fusible disconnect, Size 1, 27A, 7.5 HP at 240 VAC polyphase, 120 VAC coil, NEMA 1



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5 hp 200 V AC, 3 phase 7.5 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 60 A
NEMA size	1

### Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

### Ordering and shipping details

Category	21213-8538,39 SC,SD(NOT S*R,T,W)
----------	----------------------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	CP1
GTIN	00785901743774
Package weight(Lbs)	32.57 lb(US) (14.774 kg)
Returnability	No
Country of origin	MX

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

### Contractual warranty

Warranty	18 months
----------	-----------