

Product data sheet

Characteristics

8538SDASP4

Combination Starter, Type S, fusible disconnect, Size 2, 45A, 3 pole, 120VAC coil, Motor Logic SSOLR, NEMA 3R/12

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	45 A
Number of Poles	3P
Horsepower Rating	10 hp 200 V AC, 3 phase 10 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Solid state Motor Logic class 10/20 15...45 A
Disconnect Type	Fusible disconnect switch H and K, 60 A, electrical SPDT
NEMA size	2
Height	27.75 in (704.85 mm)
Depth	9.59 in (243.59 mm)
Width	10.5 in (266.70 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product certifications	UL Listed CSA

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901876427
Package weight(Lbs)	49.5 lb(US) (22.45 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------