

8539SDASP5

NEMA Combination Starter, Type S, HHL
electronic motor circuit protector, Size 2, 45A, 3
phase, 120 VAC coil, NEMA 12



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5...15 hp 480 V AC, 3 phase 1.5...7.5 hp 240 V AC, 3 phase
Maximum Voltage Rating	240/480 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Solid state Motor Logic class 10/20 9...27 A
Disconnect Type	Circuit breaker, 30 A, electrical SPDT
Circuit breaker type	EMCP
Breaking capacity	100 kA 480 V AC 50 kA 600 V AC
Height	27.75 in (704.85 mm)
Depth	9.59 in (243.59 mm)
Width	10.5 in (266.70 mm)
Handle Swing	3.25 in (82.55 mm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
NEMA size	2
Product certifications	UL listed file E152395 CCN NKJH UL listed file E152395 CCN NKJH7 CSA file 584 class 3211 04

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901973775
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	12.00 in (30.480 cm)
Package 1 width	14.00 in (35.560 cm)
Package 1 Length	32.50 in (82.550 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------