

Product data sheet

Characteristics

8903LO30V02

Contactor, Type L, multipole lighting, electrically held, 30A, 3 pole, 600 V, 110/120 VAC 50/60 Hz coil, open style

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz 140 VA 50 Hz
Hold-in power consumption in VA	30 VA 60 Hz 30 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	5.00 in (127 mm)
Depth	3.11 in (79 mm)
Width	2.87 in (73 mm)

Environment

Enclosure Type	Not rated (open device)
Product certifications	UL Listed CSA

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901851707
Nbr. of units in pkg.	1
Package weight(Lbs)	2.8 lb(US) (1.27 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	4.50 in (11.430 cm)
Package 1 width	6.20 in (15.748 cm)
Package 1 Length	6.90 in (17.526 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------