

Product data sheet

Characteristics

8910DPA34V02Y392

Contactor, Definite Purpose, 30A, 4 pole, 20 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, open, 2 NC power poles

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	4P
Pole contact composition	2 NO + 2 NC
Range of product	DPA

Complementary

Maximum Horse Power Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 15 hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical connection	Quick connect terminals Binder head

Environment

Product certifications	UL Recognized CSA
------------------------	----------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21343 - 8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	00785901025801
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2 lb(US) (0.54 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.30 in (8.382 cm)
Package 1 width	3.30 in (8.382 cm)
Package 1 Length	4.30 in (10.922 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	10.85 lb(US) (4.921 kg)
Package 2 Height	7.20 in (18.288 cm)
Package 2 width	7.10 in (18.034 cm)
Package 2 Length	8.60 in (21.844 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------