

Product data sheet

Characteristics

8911DPSG32V09

Starter, Definite Purpose, nonreversing, 30A, 2 pole, 1 phase, 208 to 240 VAC coil, melting alloy overload, NEMA 1

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	1 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1

Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901024699

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.	1
Package weight(Lbs)	5.75 lb(US) (2.61 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Package 1 Height	6.60 in (16.764 cm)
Package 1 width	7.10 in (18.034 cm)
Package 1 Length	11.20 in (28.448 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------