

9002AW14

Foot Switch, Harmony, industrial, pedal and side shields, 0.6A at 600 VAC, DPDT contact, NEMA 2, 4, 13 enclosure

Product availability : Stock - Normally stocked in distribution facility



Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	UL Listed CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	DPDT
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Side shield Pedal shield
Operator Action	Spring return
Rated Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.75 A 480 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 3 A 120 V AC resistive control circuit UL 508 0.2 A 125 V DC resistive control circuit UL 508
Height	4.84 in (123 mm)
Width	5.39 in (137 mm)
Depth	9.02 in (229 mm)

Ordering and shipping details

Category	21441 - 9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	00785901817413

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.	1
Package weight(Lbs)	4.52 lb(US) (2.05 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	7.80 in (19.812 cm)
Package 1 width	7.60 in (19.304 cm)
Package 1 Length	13.20 in (33.528 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------