

# Product data sheet

## Characteristics

# 9070EO1D1

## INDUSTRIAL CONTROL TRANSFORMER 50VA 220x440V PRIMARY

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Industrial Control Transformer
Range of product	EO

### Complementary

Phase	1 phase
Rated power in VA	50 VA
Primary voltage	230 x 460 V 240 x 480 V 220 x 440 V
Secondary voltage	110 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals

### Environment

Product certifications	UL Listed CSA CE
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

### Ordering and shipping details

Category	16208 - 9070 9070 AP,E,G,H,SB, T, TF, (ALL)
Discount Schedule	CP8
GTIN	00785901831617
Nbr. of units in pkg.	1

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	4.00 in (10.160 cm)
Package 1 width	4.20 in (10.668 cm)
Package 1 Length	3.70 in (9.398 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------