

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Industrial Control Transformer
Range of product	EO

Complementary

Phase	1 phase
Rated power in VA	100 VA
Primary voltage	240 x 480 V 230 x 460 V 220 x 440 V
Secondary voltage	110 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals

Environment

Product certifications	UL Listed CE CSA
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	16208 - 9070 9070 AP,E,G,H,SB, T, TF, (ALL)
Discount Schedule	CP8
GTIN	00785901837138
Nbr. of units in pkg.	1

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	3.80 in (9.652 cm)
Package 1 width	4.20 in (10.668 cm)
Package 1 Length	4.00 in (10.160 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------