

# 9070KL300D9

## INDUSTRIAL CONTROL TRANSFORMER

### 300VA MULTI-VOLTAGE WITH 610mm/24INCH LEADS

Product availability : Stock - Normally stocked in distribution facility



#### Main

Product or component type	Industrial Control Transformer
Range of product	KL

#### Complementary

Phase	1 phase
Rated power in VA	300 VA
Primary voltage	440 V 460 V 480 V
Secondary voltage	120 V 115 V 110 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Connector type	Lead 2001.31 ft (610 m)

#### Environment

Product certifications	CE UL Listed CSA
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

#### Ordering and shipping details

Category	21692 - 9070 K (NOT KF)
----------	-------------------------

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	CP8
GTIN	00785901020240
Nbr. of units in pkg.	1
Package weight(Lbs)	8.54 lb(US) (3.87 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	6.50 in (16.510 cm)
Package 1 width	6.70 in (17.018 cm)
Package 1 Length	7.70 in (19.558 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------