

# Product data sheet

## Characteristics

# 9070T350D25

Transformer, Type T, industrial control, 350 VA,  
277 VAC primary / 24 VAC secondary, 1 phase,  
50/60 Hz, 80 °C rise

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Product Type	Industrial Control Transformer
Power Rating	350 VA
Type	T

### Complementary

Number of Phases	1 phase
Power Rating	350 VA UL 350 VA CSA 350 VA NOM 250 VA
Temperature Rise	80 °C
Electrical Connection	Screw clamp terminals
Height	3.8 in (96.52 mm)
Width	4.5 in (114.30 mm)
Depth	5.09 in (129.29 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

### Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
Nbr. of units in pkg.	1
Package weight(Lbs)	10.2 lb(US) (4.63 kg)
Returnability	No
Country of origin	US

## Packing Units

Package 1 Height	6.00 in (15.240 cm)
Package 1 width	7.50 in (19.050 cm)
Package 1 Length	6.50 in (16.510 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	10 Years
----------	----------