

# Product data sheet

## Characteristics

# 9070T75Q24174R1

Transformer, Type T, industrial control, 75 VA, 208/240/277 VAC primary / 120 VAC second, 1 phase, 50/60 Hz, 55 °C rise

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Product Type	Industrial Control Transformer
Power Rating	75 VA

### Complementary

Number of Phases	1 phase
Power Rating	75 VA

### Environment

Enclosure Type	Not rated (open device)
----------------	-------------------------

### Ordering and shipping details

Category	16208 - 9070 9070 AP,E,G,H,SB, T, TF, (ALL)
Discount Schedule	CP8
GTIN	00785901323488
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

### Packing Units

Package 1 Height	3.50 in (8.890 cm)
Package 1 width	3.88 in (9.855 cm)
Package 1 Length	4.00 in (10.160 cm)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------