

Product data sheet

Characteristics

9070TF1500D1

Transformer, Type TF, industrial control, 1500 VA, 240/480 VAC primary / 120 VAC second, 1 phase, 50/60 Hz, 115 °C rise

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Industrial Control Transformer
Power Rating	1500 VA
Primary Voltage	220 x 440 V 240 x 480 V 230 x 460 V
Secondary Voltage	110 V 120 V 115 V
Type	TF

Complementary

Number of Phases	1 phase
Power Rating	1500 VA UL 1500 VA CSA 1500 VA NOM 1000 VA
Primary to Secondary Voltage	220 x 440 V 110 V 230 x 460 V 115 V 240 x 480 V 120 V
Fuse type	0.41 x 1.50 in CC top
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	7.46 in (189.48 mm)
Width	7.06 in (179.32 mm)
Depth	5.92 in (150.37 mm)
Material	Copper winding

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Fingersafe Cover Compatibility	FSC2
--------------------------------	------

Environment

Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16203 - 9070 TF (NOT T) 250-1000VA
Discount Schedule	CP8
GTIN	00785901314202
Nbr. of units in pkg.	1
Package weight(Lbs)	37.68 lb(US) (17.09 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	12.00 in (30.480 cm)
Package 1 width	11.80 in (29.972 cm)
Package 1 Length	14.80 in (37.592 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------