

# Product data sheet

## Characteristics

# 9080FB3621J

## Terminal block, Linergy, fuse holder, Class J, 60A, 600 V, 3 pole

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	9080FB
Product	Fuse holder

### Complementary

Current Rating	60 A
[Ue] rated operational voltage	<= 600 V AC/DC
Fuse type	J
Fuse size	1.0625 x 2.375 in
Number of poles	3
Electrical connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
SCCR	200 kA UL 512
Product certifications	CSA file 70360 class 6225 01 UL listed file E40747 CCN IZLT CE
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic block
Wire stripping length	0.5625 in (14.29 mm)
Terminal Tightening Torque	lugs 50 lbf.in (5.65 N.m) AWG 3...AWG 2 copper or aluminium lugs 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 14 copper
Height	4.07 in (103.38 mm)
Width	4.72 in (119.89 mm)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	2.09 in (53.09 mm)
-------	--------------------

### Ordering and shipping details

Category	21701 - 9080 FB
Discount Schedule	CP1
GTIN	00785901139669
Package weight(Lbs)	0.78 lb(US) (0.35 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 2 Weight	15.87 lb(US) (7.199 kg)
------------------	-------------------------

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

### Contractual warranty

Warranty	18 months
----------	-----------