

# Product data sheet

## Characteristics

# 9080LBA364101

Power distribution block, Linergy, 3 pole, 1 line, 1 load, 420A CU, 340A AL, 600 V

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	9080LB
Product	Power Distribution Block
Current Rating	420 A copper 340 A aluminium

### Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number of poles	3
Terminals per Pole	1 line 1 load
Wire Size	Line 1, AWG 4...600 kcmil, copper or aluminium Load 1, AWG 4...600 kcmil, copper or aluminium
Electrical Connection	Tin plated aluminium lugs
SCCR	100 kA UL 508 A
Ambient air temperature for operation	-40...302 °F (-40...150 °C)
Block Material	Phenolic block
Terminal Tightening Torque	Line lug 500 lbf.in (56.49 N.m) AWG 4...600 kcmil copper or aluminium Load lug 500 lbf.in (56.49 N.m) AWG 4...600 kcmil copper or aluminium
Wire stripping length	Line 1.38 in (35.05 mm) Load 1.38 in (35.05 mm)
Height	4.75 in (120.65 mm)
Width	2.28 in (57.91 mm)
Depth	2.91 in (73.91 mm)
End Barrier	9080LB43

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 70361 class 6228 01
----------------	--

## Ordering and shipping details

Category	21711 - 9080 LB
Discount Schedule	CP1
GTIN	00785901097495
Package weight(Lbs)	2.55 lb(US) (1.16 kg)
Returnability	Yes
Country of origin	US

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

## Contractual warranty

Warranty	18 months
----------	-----------