

Product data sheet

Characteristics

9422ATDF631

Operating mechanism, flange mounted, variable depth, 60A, 600 V, fuseholder, switch mechanism, 6 inch handle, NEMA 4

Product availability : Stock - Normally stocked in distribution facility



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 hp 200 V AC 15 hp 230 V AC 30 hp 460 V AC 50 hp 575 V AC 10 hp 250 V DC
Fuse Rating	60 A 600 V
Handle Type	6 in handle included NEMA 1/3/3R/4 enclosures sheet steel
Fuse Type	J R H K

Environment

Certifications	UL Recognized CSA
----------------	----------------------

Ordering and shipping details

Category	21732 - 9422
----------	--------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	CP1
GTIN	00785901872191
Nbr. of units in pkg.	1
Package weight(Lbs)	9.05 lb(US) (4.11 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.10 in (18.034 cm)
Package 1 width	11.20 in (28.448 cm)
Package 1 Length	16.00 in (40.64 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------