

Product data sheet

Characteristics

9422TEF10

Operating mechanism, flange mounted, variable depth, 100A, 600 V, H, K, J, R fuseholder, switch mechanism

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

| | |
|-----------------|---------------------------|
| Range | 9422T |
| Product | Disconnect Switch |
| Disconnect Type | Fusible disconnect switch |

Complementary

| | |
|-------------------|--|
| Mounting Type | Flange rod variable depth |
| Current Rating | 100 A |
| Horsepower Rating | 25 hp 200 V AC 30 hp 230 V AC 60 hp 460 V AC 75 hp 575 V AC 20 hp 250 V DC |
| Fuse Rating | 100 A 250/600 V |
| Handle Type | Ordered separately |
| Fuse Type | J R K H |

Environment

| | |
|----------------|----------------------|
| Certifications | UL Recognized CSA |
|----------------|----------------------|

Ordering and shipping details

| | |
|----------|--------------|
| Category | 21732 - 9422 |
|----------|--------------|

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-----------------------|-----------------------|
| Discount Schedule | CP1 |
| GTIN | 00785901879831 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 6.97 lb(US) (3.16 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 7.00 in (17.78 cm) |
| Package 1 width | 11.20 in (28.448 cm) |
| Package 1 Length | 16.00 in (40.64 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|