

Product data sheet

Characteristics

9998LH44

Replacement coil, 110/120 VAC 50/60 Hz, 8903L
Contactor, 8 to 12 poles

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Coil
Accessory / separate part destination	Class 8903 contactor

Complementary

[Ue] rated operational voltage	120 V AC 60 Hz 110 V AC 50 Hz
Inrush power in VA	170 VA 180 VA
Average consumption	35 VA
Height	2.38 in (60.5 mm)
Width	2.11 in (53.6 mm)
Depth	1.46 in (37.1 mm)

Ordering and shipping details

Category	21756 - 9998 DISCOUNT CP10
Discount Schedule	CP10
GTIN	00785901081289
Package weight(Lbs)	0.36 lb(US) (0.16 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

Warranty	18 months
----------	-----------
