

# Product data sheet

## Characteristics

# 9999SA2

## Start Stop push button kit, NEMA 1, Type S contactors and starters

Product availability : Stock - Normally stocked in distribution facility



### Main

Product Range	Type S
Component type	Push-button
Used with	contactor starter

### Complementary

NEMA size	1 00 2 0 3
Marking	START-STOP
Mounting mode	Panel-mounted
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A 600 V AC resistive control circuit UL 508
Height	1.02 in (25.8 mm)
Width	2.58 in (65.5 mm)
Depth	24.00 in (609.6 mm)
Net Weight	0.37 lb(US) (0.17 kg)

### Environment

NEMA degree of protection	NEMA 1
Product certifications	CSA UL Listed UL Recognized

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901867234
Package weight(Lbs)	0.37 lb(US) (0.17 kg)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Under investigation
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

## Contractual warranty

Warranty	18 months
----------	-----------