

Product availability : Stock - Normally stocked in distribution facility



Main

Product Range	Type S
Component type	Selector switch
Used with	contactor starter

Complementary

NEMA size	00 1 0 2 3
Marking	HAND-OFF-AUTO
Mounting mode	Panel-mounted
Rated breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 5 A 600 V AC resistive control circuit UL 508
Height	1.88 in (47.75 mm)
Width	3.81 in (96.77 mm)
Depth	5.63 in (143.00 mm)
Net Weight	0.51 lb(US) (0.23 kg)

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL Listed UL Recognized CSA

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901783008
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------