

Product availability : Stock - Normally stocked in distribution facility



Main

Product Range	Type S
Component type	Selector switch
Used with	contactor starter

Complementary

NEMA size	0 4 00 5 1 3 2 6 7
Marking	HAND-OFF-AUTO
Mounting mode	Panel-mounted
Rated breaking capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 10 A 600 V AC resistive control circuit UL 508 1.1 A 125 V DC resistive control circuit UL 508 0.55 A 250 V DC resistive control circuit UL 508 0.2 A 600 V DC resistive control circuit UL 508
Height	1.88 in (47.75 mm)
Width	3.81 in (96.77 mm)
Depth	5.63 in (143.00 mm)
Net Weight	0.82 lb(US) (0.37 kg)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL Recognized CSA

Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901030164
Package weight(Lbs)	0.82 lb(US) (0.37 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------