

Product data sheet

Characteristics

9999SP28R

NEMA Motor Starter and contactor, Type S, pilot light kit, incandescent, red and green, 120 VAC 60 Hz, Type 1, 3R, 12

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Product Range	Type S
Component type	Pilot light kit
Used with	contactor starter

Complementary

NEMA size	00 0 4 2 6 3 7 5 1
Signalling colour	Green/red
[Uc] control circuit voltage	120 V AC 60 Hz
Kit composition	1 pilot light 2 cable clips 2 instructions 2 cap

Environment

NEMA degree of protection	NEMA 12 NEMA 1 NEMA 4
Product certifications	CSA UL Recognized

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901030188
Nbr. of units in pkg.	1
Package weight(Lbs)	0.83 lb(US) (0.38 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	3.30 in (8.382 cm)
Package 1 width	4.40 in (11.176 cm)
Package 1 Length	6.40 in (16.256 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------