

Product data sheet

Characteristics

9999SX7

Auxiliary contact, Type S, 1 NC contact, external, field convertible

Product availability : Stock - Normally stocked in distribution facility



Main

Product Range	Type S
Component type	Auxiliary Contact Module
Used with	contactor starter

Complementary

NEMA size	2 0 1 6 3 5 00 4 7
Auxiliary contact composition	1 NC
[Uc] control circuit voltage	<= 600 V AC 50/60 Hz
Rated breaking capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508

Environment

Product certifications	CSA UL Recognized UL Listed
------------------------	-----------------------------------

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	21761 - 9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901733508
Nbr. of units in pkg.	1
Package weight(Lbs)	0.22 lb(US) (0.10 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.50 in (3.81 cm)
Package 1 width	3.10 in (7.874 cm)
Package 1 Length	4.50 in (11.43 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------