

Product data sheet

Characteristics

QOC342MQF

Replacement cover, QO, for 42 space load center with QDL main breaker, flush, gray



Product availability: Stock - Normally stocked in distribution facility

Price*: 92.00 USD



Main

Range of Product	QO
Product or Component Type	Load Center Cover

Complementary

Cover type	Flush cover
Product Compatibility	For indoor load center
Surface finish	Baked enamel Gray
Number of spaces	42
Height	40.57 In (1030.48 mm)
Width	15.44 In (392.18 mm)
Depth	0.7 In (17.8 mm)
Tightening torque	Cover 2.3 N.m

Ordering and shipping details

Category	US10DE300011
Discount Schedule	0DE3
GTIN	785901290650
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.00 In (5.080 cm)
Package 1 Width	15.80 In (40.132 cm)
Package 1 Length	40.90 In (103.886 cm)
Package 1 Weight	14.381 Lb(US) (6.523 kg)
Unit Type of Package 2	PAL

Number of Units in Package 2	60
Package 2 Height	40.00 In (101.600 cm)
Package 2 Width	40.00 In (101.600 cm)
Package 2 Length	48.00 In (121.920 cm)
Package 2 Weight	917.0003 Lb(US) (415.944 kg)

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg CO2 eq, Total Life cycle)	50

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**